

MEDISURE 30G

Detergent-Disinfectant Sachet (NSF D1)

Built for compliance. Trusted for performance.

Medisure 30G is a pre-measured, chlorine-based detergent-disinfectant in a convenient single-dose sachet. Cleans and disinfects in one step, delivering consistent 250 ppm available chlorine for reliable, repeatable results in food and hygiene-critical environments.

 <p>PRE-MEASURED FOR ACCURACY</p> <p>Pre-measured sachet ensures accurate dosing every time, eliminating incorrect dilution.</p>	 <p>CLEANS & DISINFECTS IN ONE STEP</p> <p>Powerful dual-action formula removes soil and kills bacteria effectively.</p>	 <p>CONSISTENT PERFORMANCE</p> <p>Delivers a consistent 250 ppm chlorine for reliable, repeatable hygiene outcomes.</p>	 <p>FOOD INDUSTRY SAFE</p> <p>NSF D1 Registered for use in food processing and hygiene-critical environments.</p>
---	--	--	--



D1 REGISTERED

NSF D1 Registered for use in food processing and preparation areas.

STEP-BY-STEP APPLICATION GUIDE

	<p>30G SACHET</p> <ul style="list-style-type: none"> Pre-measured for accuracy Easy to use Fast dissolving Consistent performance
	<p>BOX OF 100 SACHETS</p> <ul style="list-style-type: none"> Cost effective Easy storage Convenient dispensing
	<p>BOX OF 500 SACHETS</p> <ul style="list-style-type: none"> Cost effective Easy storage Convenient dispensing

<p>1 DISSOLVE</p>  <p>Dissolve 1 sachet (30g) in 10 litres of cold or warm (not hot) water. Stir to ensure complete dissolution.</p>	<p>2 APPLY</p>  <p>Apply solution using a clean cloth or mop to surfaces to be cleaned and disinfected.</p>	<p>3 CONTACT TIME</p>  <p>Leave for a minimum of 5 minutes to ensure effective cleaning and disinfection.</p>	<p>4 RINSE</p>  <p>Rinse food contact surfaces thoroughly with clean potable water.</p>	<p>5 AIR DRY</p>  <p>Allow surfaces to air dry before use or further processing.</p>
--	--	---	---	--

1 SACHET (30g) = 10 LITRES OF COLD OR WARM (NOT HOT) WATER = ± 250 PPM AVAILABLE CHLORINE

<p>KEY BENEFITS</p> <ul style="list-style-type: none"> Pre-measured for accurate dosing every time Cleans and disinfects in one step Delivers consistent 250 ppm chlorine Reduces operator error and training requirements Portable and easy to use 	<p>BROAD SPECTRUM DISINFECTION</p>  <p>Effective against a wide range of bacteria in food and hygiene environments.</p>	<p>IDEAL FOR USE IN</p> <table border="0"> <tr> <td> Food Processing & Preparation Areas</td> <td> Healthcare Environments</td> <td> Equipment & Food Contact Surfaces</td> <td> Cold Rooms & Storage Areas</td> </tr> </table>	 Food Processing & Preparation Areas	 Healthcare Environments	 Equipment & Food Contact Surfaces	 Cold Rooms & Storage Areas	<p>NSF D1 REGISTERED</p>  <p>Registered for use in food processing and hygiene-critical environments.</p>	<p>WHY IT MATTERS</p> <ul style="list-style-type: none"> Eliminates incorrect dilution risk Ensures consistent hygiene standards Ideal for multi-site or staff-rotating environments
 Food Processing & Preparation Areas	 Healthcare Environments	 Equipment & Food Contact Surfaces	 Cold Rooms & Storage Areas					

TECHNICAL INFORMATION

- Format: Sachet (powder)
- Active: Chlorine (SDIC system)
- Output: ±250 ppm chlorine

DIRECTIONS FOR USE (SUMMARY)

- Dissolve 1 sachet (30g) in 10 litres of cold or warm (not hot) water.
- Apply solution using cloth or mop to surfaces.
- Leave for a minimum of 5 minutes.
- Rinse food contact surfaces thoroughly.
- Allow surfaces to air dry before use.

SAFETY INFORMATION



- Wear gloves and eye protection.
- Avoid contact with skin and eyes.
- Do not mix with acids or other chemicals.
- Store in a cool, dry place.
- Keep out of reach of children.
- For external use only.

APPLICATIONS

- Food Processing and Preparation Areas
- Healthcare Environments
- Equipment and Food Contact Surfaces
- Cold Rooms and Storage Areas

BUILT FOR COMPLIANCE. TRUSTED FOR PERFORMANCE.



SAFE FOR FOOD ENVIRONMENTS.